

classiX® all-steel bar clamps

Bar clamps for industrial application



Simply better.

An opening price point offering that embodies the stringent quality requirements of BESSEY®.

Features & Benefits

Choices

The classiX® line is an abbreviated range of the most popular global clamp performance characteristics. A variety of throat depths, pad/swivel styles and clamping capacities provide professionals with a choice that makes sense for real-world applications.

Quality

Internationally sourced components coordinated by BESSEY® quality control and engineering departments ensure great prices and great quality.

Standard pads and heavy duty pads

The standard swivel pads and heavy duty pads are tried and true contact surfaces for use with your classiX clamps. Field replaceable.

Hardened spindle

Heat-treated, high carbon Acme threaded spindle is manufactured to offer high load capacity, durability and spatter resistance.



	Clamping Capacity	Throat Depth	Clamping Force	Approx. Weight
classiX® - Standard pad				
GS12-8K	4"	3 1/8"	550 lbs.	0.5 lbs.
GS16K	6"	3 1/8"	550 lbs.	0.6 lbs.
GS20K	8"	4"	880 lbs.	1.8 lbs.
GS16-12K	6"	4 3/4"	1000 lbs.	2.0 lbs.
GS25K	10"	4 3/4"	1000 lbs.	2.5 lbs.
GS30K	12"	5 1/2"	1200 lbs.	4.3 lbs.
GS60K	24"	4 3/4"	1200 lbs.	5.1 lbs.

Grainger #

19C713

19C714

19C716

19C715

19C717

19C718

19C719

classiX® - Heavy duty pad

GSL30	12"	4 3/4"	1880 lbs.	5.0 lbs.
GSL60	24"	4 3/4"	1880 lbs.	6.5 lbs.
GSM20	7 1/2"	4 3/4"	2660 lbs.	5.2 lbs.
GSM25	9"	5 1/2"	2660 lbs.	6.0 lbs.
GSM30	12"	5 1/2"	2660 lbs.	7.0 lbs.
GSM40	16"	5 1/2"	2660 lbs.	7.5 lbs.
GSM50	20"	5 1/2"	2660 lbs.	7.7 lbs.
GSM60	24"	5 1/2"	2660 lbs.	8.0 lbs.

19C720

19C721

44ZL48

19C722

19C723

19C724

19C725

19C726

classiX® - Lever bar clamp

GSH12	4"	2 3/8"	400 lbs.	1.10 lbs.
GSH20	8"	4"	600 lbs.	2.50 lbs.
GSH30	12"	5 1/2"	1110 lbs.	5.00 lbs.
GSH50	20"	4 3/4"	1110 lbs.	6.25 lbs.

AVAILABLE

THRU

GRAINGER SOURCING

classiX® GSH all-steel lever bar clamps

- Quick – up to 5 times faster than regular clamps!
- Secure, unaffected by vibrations.
- Strong – high clamping force up to 1110 lbs.
- Non-slip trigger release.



Standard pad



Heavy duty pad



Rev. Jun/14

