



COM1200-RND



COM1200-SQ



COM750-RND



COM750-SQ

► Commander™ 1200 and 750 Series | Work Lights

FEATURES

- High powered LED work light.
- 1200 or 750 lumen models.
- Effective flood light solution.
- Adjustable vertical and horizontal mounts.
- Vibration resistant construction.
- Stainless steel hardware kit and u-bracket included.
- 12/24 VDC.
- Three-year LED warranty.

APPLICATIONS

- Tractors
- Tow and recovery vehicles
- Off-road vehicles
- Pick-up trucks
- Recreational vehicles

Built to Stand up to the Most Punishing Conditions

Federal Signal's Commander™ 1200 and 750 series work lights are built to go the distance, enduring the toughest conditions that a work truck can dish out. Ideal for tractors, tow and recovery, off-road, and personal vehicles, these work lights are made of a heavy-duty powder coated die cast aluminum and vibration resistant construction.

A Versatile and Effective Flood Light Solution

The Commander 1200 and 750 series work lights include a stainless steel hardware kit and u-bracket allowing the user to adjust the work light horizontally and vertically to put light wherever it is needed. 1200 and 750 series are both available in round and square options.

HOW TO ORDER

Specify model

COM1200-RND	1200 Lumen, Round
COM1200-SQ	1200 Lumen, Square
COM750-RND	750 Lumen, Round
COM750-SQ	750 Lumen, Square

SPECIFICATIONS

	COM1200-RND	COM1200-SQ	COM750-RND	COM750-SQ
Specifications				
Amp Draw	2A @ 12.8 VDC	2A @ 12.8 VDC	1.25A @ 12.8 VDC	1.25A @ 12.8 VDC
Wattage Lamp	27 Watts	27 Watts	16.6 Watts	16.6 Watts
Physical Specifications				
Height	5.7 in (14.5 cm)	5.6 in (14.2 cm)	5.5 in (14.0 cm)	5.6 in (14.2 cm)
Diameter	4.6 in (11.7 cm)	4.3 in (11.0 cm)	4.6 in (11.7 cm)	4.3 in (11.0 cm)
Depth	2.6 in (6.6 cm)	2.6 in (6.6 cm)	5 in (5.0 cm)	2.4 cm (6.1 cm)
Ship Weight				
	1.8 lbs (0.8 kg)	2.0 lbs (0.9 kg)	1.25 lbs (0.6 kg)	1.6 lbs (0.7 kg)



Commander is a trademark of Federal Signal Corporation.

©2015 Federal Signal Corporation. M8033 I 615