



#### NOTES:

1. ITEM: Elbow, 45°
2. PIPE SIZE - PIPE FITTING: 3/4"
3. FITTING CONNECTION TYPE: FNPT
4. FITTING SCHEDULE/CLASS: Class 3000
5. MAX. PRESSURE: 3000 psi@100°F
6. PIPE FITTING MATERIAL: 304 Stainless Steel
7. STANDARDS: Material Conforms To ASTM-A-182,  
Threads Conform To ANSI/ASME B1.20.1 meets ASME B16.11



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

1.00

COMPONENT

Stainless Steel Pipe Fitting

2UA64

Elbow, 45 Deg, 3/4 In, 304 Stainless Steel

UNIT

INCH

SHEET

1 of 1